

EL420HD

Two-part high hardness, room temperature curing polyurethane resin

Application	Key Properties
-------------	----------------

- Encapsulation of electrical and electronic devices
- Optical instruments
- High quality castings

- Excellent long-term UV stability
- Scratch and mark resistant
- Meets requirements of WEEE & RoHS
- High mechanical strength
- Easy to mix and process
- Mercury Free

Description

- Basic Two-component polyurethane system
- Resin RL420HD
- Hardener HL420HD

Physical Data (approx. – values)	Resin	Hardener	Mixed
Colour	Clear	Clear	Clear
Specific Gravity	1.05	1.13	1.09
Viscosity (mPas) @ RT	2500	1200	1700

Cure Schedule (100ml)	Working Life	Gel Time	Light Handling	Full Cure
Temperature	(minutes)	(minutes)	(hours)	(hours)
RT*	30	40	48	72
40°C	-	-	24	24
60°C	-	-	12	12

*RT is defined as 20-25°C

The above are typical values and will vary depending on the cured mass and application. Hotter temperatures may be used for faster cure but will result in higher post cure shrinkage and higher cure exotherm. Experimentation and testing is suggested to avoid side effects. For maximum properties a post cure may be required – Contact our technical service department for advice.

Processing

Mix ratio by weight 0.93:1
 Mix ratio by volume 1:1

Approvals	
RoHS compliant	Yes (Hg Free)
UL94-V0	No
REACH (SVHC concentration)	Refer to SDS

Typical Properties	Result	Unit
Tack Free time	<2ml @ RT	240 minutes
Water Absorption	(30 days @25°C)	0.87 %
Hardness		80 Shore D
Operating Temperature		- 55 to + 120 °C (application & geometry dependent)
Thermal Conductivity		0.25 W/mK
Tensile Strength		26 MPa
Elongation at Break		5-10 %
Compressive Yield Strength		30 MPa
Coefficient of Linear Expansion		60-80 pp/m°C
Volume Resistivity		3 x 10 ¹⁴ ohm.cm
Surface Resistivity		3 x 10 ¹⁵ ohm
Electric Strength		20 kV/mm
Refractive Index		1.47-1.48

Packaging

EL420HD is available in Bulk, Twinpacks and cartridges

Availability

Available through sales@robnor.co.uk and www.robnor-resinlab.com

Cartridge Part Numbers

EL420HD/NC/050TC	

It is essential for best results that the cartridge is 'balanced' before use to ensure correct mixing. Loading the cartridge into the gun before attaching the mixer element and pumping the gun to push a small amount of the contents forward will achieve this. Wipe the excess from the cartridge tip and add the static mixer. The cartridge is now ready for use.

Twinpacks - Part Numbers

EL420HD/NC/100	EL420HD/NC/500
EL420HD/NC/250	

Twinpacks are pre-weighed resin and hardener components contained in a tough flexible film, separated by a removable clip and rail. Once the clip and rail has been removed the resin and hardener is thoroughly mixed within the bag and is immediately ready for use. Mixing will normally take ~ 2 minutes due to the viscosity; but pay special attention to the corners. Twinpacks are ideal for small to medium production runs, prototyping and on-site or field use. The twinpack weight/volume may also be tailored to a specific size on request.

For further details please visit www.robnor-resinlab.com

Bulk - Part Numbers

RL420HD/NC/5KG	HL420HD/NC/5KG
RL420HD/NC/20KG	HL420HD/NC/20KG

Both resin and hardener are supplied in 5kg, 25kg and 200ltr drums and fully evacuated and ready for use. Care should be taken to ensure when mixing the resins air is not entrained in the mixture. If this is unavoidable the mixed resin and hardener should be re-evacuated before dispensing. The bulk resin and hardener materials can be dispensed from suitable dispensing machinery, details provided by Fluid Research on request.

Kits and Sets - Part Numbers

	EL420HD/NC/5KGSET
	EL420HD/NC/10KGSET

Kits and Sets are provided in separate containers to the correct ratio. In Kit form, pour the contents of the smaller container into the larger container and use it as a mixing vessel. Stir well using an appropriate mixer until homogeneous.

Note: Incomplete mixing will be characterised by erratic or partially incomplete cure even after extended time periods.

Cleaning

All equipment contaminated with mixed material should be cleaned before the material has hardened. TS130 is a suitable non-flammable cleaning agent, although other solvents may be found suitable. TS130 will also remove cured material provided it can soak for several hours.

Storage and Shelf Life

12 months at 5 °C in cartridges that are foil wrapped and desiccant packed. Store horizontally.

Bulk containers should be inverted every two to three weeks to reduce the accumulation of the fillers on the bottom of the containers.

Isocyanates are sensitive to moisture and should be kept in their original container or in a volume tank under dry nitrogen blanketing. Many isocyanates are prone to dimerization, the formation of a white precipitate. Products with minor amounts of this precipitate normally cure to full properties.

Storage at 20 +/- 5 °C (60 °F to 86 °F) is recommended to ensure full shelf life.

Health and Safety

Please refer to RL/HL420HD Health and Safety data or our Technical Service Department for individual/specific advice.

Copyright & Warranty - Robnor Resinlab Limited

The results and information above does not constitute a specification and is given in good faith and without warranty. The information is derived from test/or extrapolations believed to be reliable and is quoted for guidance only. The product is offered for evaluation on the understanding the customer satisfies himself that the product is suitable for the intended application by proper evaluation and testing.

Contact Details

Robnor Resinlab Limited
31 Athena Avenue
Elgin Industrial Estate
Swindon
SN2 8EJ
United Kingdom

Tel: +44 (0) 1793 823741
Fax: +44 (0) 1793 827033
Email: support@robnor.co.uk
Buy Online: www.robnor-resinlab.com (UK only)